

PVI00589EN_V01

Sampler Compact hand sampler

- Compact and space-saving design
- Suitable for good flowing products
- Manual sampling
- Up to 95ml per sampling possible
- Simple 180° turning movement for sampling
- Screw thread for custom sample bottles
- Endless-Foil unit for containment applications
- Easy disassembly and easy cleaning
- Ex-version according to ATEX available



Function

The hand sampler is used to take any number of samples of the same size from a product stream. The samples are collected in rigid containers or in plastic bags using the Novindustria endless foil system, resulting in a representative total sample. The products must be free-flowing, they must have low adhesive properties, they must fall freely out of the hand sampler rod and they must not stick in the subsequent transition funnel.

The hand sampler is installed in downcomers, usually after dosing and before discharge equipment, in order to be able to take solids samples from closed systems.

